			0	₩	A	
Z'	ØS					
			LAYOUT SHOWN AS	EXAMPLE		
	Keying Shown as example					
CHARACTERISTICS	Connector dimension					
-Standard : Based on MIL-DTL-38999 Series III	DimNominalØS44.9 Max	[				
-Shell Material : Composite -Shell Plating : Nickel -Insulator : Thermoplastic	Z' 31.5 Max VV THREAD M34x1-6g		SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)			
-Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer			Cour	try Jurisdiction & Control Li	ict	
-Contact Plating : Gold over copper Alloy 0.8µm minimum			Cour		st	
-Durability : 500 Mating cycles			PN: 8D523M55BA			
-Delivered with Souriau contacts and Accessories				···· <b>·····</b>		
-Temperature Range : -65°C to +200°C -Salt Spray : 2000 hours		A 07-10-201	16 First Release			
Mass : 65.3 g ± 10%		ISS DATE Designed By:	Latest modification - by Date:	CUSTOMER DR	MOD N°	
		TITLE				
BASIC SERIES: 8D 5 - 23 N	И 55 В А	SCALE	General linear	NPRDS / PRO	JECT	
SHELL TYPE : Plug with RFI Shielding		NA	t	859		
CONTACT TYPE : Standard Crimp Contact			SOURIAU WWW.SOURIAU.COM it must not be reproduced or communicated without permission			
CONTACT TYPE : Standard Crimp Contact SHELL SIZE : 23	CONTACT TYPE : SOCKET(500	Matings)		communicated	without permission	
	CONTACT TYPE : SOCKET(500 CONTACT LAYOU		SOURIA	J DRG N°	SHEET	

F	Ŧ	۵	н <b>т</b>	m	D	0
		Contact Layout				
4	x (n	$\begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \\ \\ \end{array} \\ \\ \end{array} \\ \\ \end{array} \\ \begin{array}{c} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} $				
	B +.225 (5.72) C +.336 (8.53) D +.450 (11.43)	Contacts (Insert arrangement 23-55)           On         Contact position ID         Location           Y-axis (mm)         Contact position ID         X-axis (mm)         Y-axis (mm)           +455 (11:56)         f         -112 (2.84)         -325 (8.26)           +326 (8.26)         h         -336 (8.53)         -195 (4.95)           +130 (3.30)         i         -336 (8.53)         -065 (1.65)           -130 (3.00)         j         -336 (8.53)         +055 (1.55)           -325 (8.26)         m         -225 (5.72)         +260 (6.60)           -332 (8.25)         m         -225 (5.72)         +260 (6.60)           -330 (9.94)         n         -112 (2.84)         +325 (8.26)           -326 (9.94)         n         -225 (5.72)         +260 (6.60)           -390 (9.94)         n         -112 (2.84)         +325 (8.26)				
ω	$\begin{array}{c c c c c c c c c c c c c c c c c c c $	$\begin{array}{c c c c c c c c c c c c c c c c c c c $				
	size no. cont	ber of Size Service Contact Superseder lacts contacts rating location	8			SOURIAU shall not be liable for an
						due to a use of the Products wl the Specifications issued by either o (professional recommenda
N						Count
						PN: 8D523N
_					A 07-10-20 ISS DATE Designed By:	116 First Release Latest modification - by Date:
					TITLE	Compo
_					SCALE NA	General linear Tolerances: ±
					SOURIA	U WWW.SOURIAU.C
					FORMAT A3	SOURIAU 8D523M
L	Н	G	F	E	D	C

