

Φ		A				
100/				4		
Ma						
a ce	-					
S EXAMPLE				3		
any non-conformit	w or damage					
which does not co	any non-conformity or damage which does not comply with					
r of the Parties or by a third party dation, technical notice.)						
Intry Juriso						
				2		
SW04SAL						
	CUSTOMER	DRAWING	MOD N°			
um Receptac	e 8D serie	25				
ar	NPRDS / I	PROJECT				
	85			1		
I.COM	.COM This document is the property of SOURIAU it must not be reproduced or					
		communicated without permission				
U DRG N° N04SAL-C			SHEET 1/2			
B		Α		J		

r		۵	н т	т		0	
		Contact Layout				Panel cutout	
4						JAM NUT RECEPTACLE (TYPE 7)	
	B +203 (5-16) + C +324 (823) - D +424 (10.77) - E +493 (12.52) - F +531 (13.49) - G +531 (13.49) - H +493 (12.52) - J +424 (10.77) - K +324 (8.23) - L +203 (5.16) -	Contacts V-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) 531 (13.49) f +412 (10.46) +000 (0.00) +495 (12.57) g +377 (9.58) -132 (3.35) -425 (10.80) h +311 (7.90) -251 (6.38) -326 (8.28) k +212 (5.38) -344 (8.74) -205 (5.21) m +086 (2.18) -397 (10.08) -069 (1.75) p -212 (5.38) -344 (8.74) -205 (5.21) q -311 (7.90) -251 (6.38) -326 (8.28) r -377 (9.58) -132 (3.35) -425 (10.80) s -412 (10.46) +000 (0.00) -435 (12.57) t -377 (9.58) -132 (3.35) -326 (8.28) r -377 (9.58) -132 (3.35) -425 (10.80) s -412 (10.46) +000 (0.00) -455 (12.57) t -377 (9.58) -132 (3.35) -534 (13.49) u -311 (7.90) +251 (6.38)				ØC	
ယ	N 069 (1.75) P 203 (5.16) R 324 (8.23) S 424 (10.77) T 493 (12.52) U 531 (13.49) V 531 (13.49) W 493 (12.52) Contact Location	-531 (13.49) v -212 (5.38) +344 (8.74) -495 (12.57) w -086 (2.18) +397 (10.08) -425 (10.80) x +009 (1.75) +263 (6.68) -326 (8.28) y +172 (4.37) +149 (3.78) -205 (5.21) z +268 (6.55) +000 (0.00) -099 (1.75) BB +.069 (1.75) -263 (6.68) +205 (5.21) CC 069 (1.75) -263 (6.68) -205 (5.21) CC 069 (1.75) -263 (6.68) -205 (5.21) CC 069 (1.75) -263 (6.68) Contacts (insert arrangement 25-4) u Location				Dim Nomina B 43.43+0/-0 ØC 44.7+0.25).25
	Y324 (8.23) Z -203 (5.16) a -069 (1.75) b +086 (2.18) c +212 (5.38) d +.311 (7.90)	T-aus position ID A-aus T-aus (mm) (mm) (mm) (mm) +326 (8-28) DD -172 (4.37) -149 (3.78) +425 (10.80) EE -258 (6.55) +.000 (0.00) +425 (13.49) GG 069 (1.75) +263 (6.83) +337 (10.08) HH +.000 (0.00) +.132 (3.85) +344 (8.74) JJ +.086 (2.18) +.000 (0.00) +251 (6.38) KK +.000 (0.00) 132 (3.35) +.132 (3.35) LL 086 (2.18) +.000 (0.00)	1			SOURIAU shall not be lia	
	size no. cont 25 -4 8 46	acts contacts rating location 16 I y, z, AA, DD, EE, FF, LL, JJ MS20057-4				due to a use of the Pr the Specifications issued b (professional reco	y either of t
N							Country FR
					A 05-10-20	PN: 8D	9725W
					ISS DATE Designed By:	Latest modification - by Date:	
					SCALE		minium
_					NA		trances:
					SOURIA		
					FORMAT A3		JRIAU 25W0
-	Н	G	F	E	D	С	

Φ	Þ	
Ν		4
		3
any non-conformits which does not co er of the Parties or b ndation, technical n untry Jurisc FR SWO4SAL	mply with by a third party	2
um Receptac	CUSTOMER DRAWING	
ar	NPRDS / PROJECT 859 This document is the property of	1
U.COM NU DRG N° N04SAL-C	SOURIAU it must not be reproduced or communicated without permission SHEET 2/2	
B	A	J