## DESCRIPTION: 970 SERIES D-SUB BACKSHELL

## BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) 4-40 THUMBSCREWS
- (2) HOUSING SCREWS/NUTS
- (1) SET OF COMPRESSION INSERTS VARIOUS SIZES Ø0.157 [4.0], Ø0.197 [5.0], Ø0.276 [7.0], Ø0.354 [9.0]

MATERIAL:

NICKEL PLATED ABS VH-0800

UL 94-HB

JACKSCREWS: M3 HOODSCREWS: ZINC PLATED STEEL ZINC PLATED STEEL

COMPRESSION INSERT:

ABS UL 94-HB


M3 NUT:

ZINC PLATED STEEL


OPERATING TEMP:

-55°C TO +110°C

\*\*NOTE: 3 in-lbs IS RECOMMENDED TORQUE FOR HOUSING SCREWS



DIMENSIONS (in/mm)				
No. OF PINS	Α	В	С	D
9	1.240	0.984	1.594	0.591
	31.50	24.99	40.50	15.00
15	1.575	1.312	1.594	0.591
	40.00	33.32	40.50	15.00
25	2.126	1.852	1.949	0.591
	54.00	47.04	49.50	15.00
37	2.776	2.500	2.146	0.630
	70.50	63.50	54.50	16.00



UNITS = INCHES [MM]



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp


DRAWN:
PAM JENKINS
6-09-05


SCALE
NTS
SHEET
1
2
REV
15

DWG NO.


970-YYY-020R121

RoHS COMPLIANT





## UNITS = INCHES [MM]



ROHS COMPLIANT