

Material

- ① Insulating body: Thermoplastic (UL94V-0), GREY
- ② Insulating cover: Thermoplastic (UL94V-0), GREY
- ③ Insulating lever: Thermoplastic (UL94V-0), GREY
- ④ Contact pin: Brass, Tin plated
- ⑤ Spring clamp: Stainless steel

Electrical cULus

Voltage rating: 300V  
 Current rating: 6A  
 Wire range:  
 Solid wire(AWG): 16-26  
 Stranded wire(AWG): 16-26  
 Wire strip length: 6-7mm  
 Withstanding Voltage: 1.6KV  
 Operating temperature: -40°C to +115°C  
 Soldering temperature: 250°C±10°C/5 Sec  
 Safety Approval: us


DIMENSION

L	Nx5.0+1.00
P	(N-1)x5.0

N=Number of poles

Poles	Tolerance	
	DIM L	DIM P
1p-4p	±0.15	±0.15
5p-9p	±0.20	±0.20
10p-14p	±0.30	±0.30
15p-19p	±0.40	±0.40
20p-24p	±0.50	±0.50

**RoHS compliant**  
Unit: mm



Scale	1:1					Date	Name	Customer-No.
TOLERANCE						Drawn	Alex	ASSMANN WSW-No. <b>A-TB500-HXxxH</b>
X.	±0.50					Approved	Joanna	
X.X	±0.30							Drawing-No.
X.XX	±0.10							<b>ASS 4123 CO</b>
DIM	TOL	①	Add UL	18.04.2016	Joanna			
X.°	±1°	②	Drawn	19.04.2010	Alex			Replace
Angle	TOL	Id.	Modification	Date	Name			