

1

2

3

4

5

6

7

A

B

C

D

E

F

G

H

A

B

C




D

E

F

G

H



NOTES

Material

1. Terminal body (contact pin): Brass (CuZn) Tin plated
2. Insulator (housing): Thermoplastic (UL94V-0)

④ Electrical cULus


1. Voltage rating: 300VAC
2. Current rating: 20A
3. Withstanding Voltage: 1.6KV
4. Operating temperature: -40°C to +115°C
5. Soldering temperature: 250°C ± 10°C / 5 Sec
6. Safety Approval: US

Order code:

A-TB508-OQxxCV-xx

No. of contact:
02-24PinColor of insulator
Blank: Green
BK: Black

P.C.B LAYOUT



RoHS compliant
Unit: mm

④ **US**
File No.: E349947

Scale	1:1	Date	04.05.2009	Name	Dean	Customer-No.	
TOLERANCE		Drawn	04.05.2009	Dean			
X.	±0.50	④ Update UL logo and notes	12.04.2022	Daniel	Approved	12.04.2022	Daniel
X.X	±0.30	③ Add P/N	28.04.2021	Daniel			
X.XX	±0.10	② Update	09.01.2009	Amy			
DIM	TOL	① Drawn	04.05.2009	Dean			
X.°	±1°						
X.X°	±X°						
Angle	TOL	Id.	Modification	Date	Name		

ASSMANN
WSW components

ASSMANN WSW-No.
A-TB508-OQxxCV-xx

Drawing-No.
ASS 3502 CO rev04

Replace Sheet

1

2

3

4

5

6

7

SV1482