



## MATERIALS:

- HOUSING-PBT POLYESTER UL94V-0 MIXED GLASS FIBER. STANDARD COLOR-BLACK.
- CONTACTS-0.35mm THICK PHOS-BRONZE PLATED WITH HARD GOLD AND GOLD FLASH IN SOLDER AREA.
- SHIELD-0.25mm THICK COPPER ALLOY, PLATED WITH NICKEL.

CAVITY CONFIRMS TO FCC RULES AND REGULATIONS PART 68.SUBPART F.

## Current = 1.5A max





Ref.

\*Note: AJT33L has replaced the AJT30L series. Pricing and specifications subject to change. Please review before ordering.

Tolerance unless otherwise specified

.0 ± .25 .00 ± .13 .000 ± .05 CONNECT

P/N: AJT33L881X-0X4 \*

Desc.: Side entry, shielded, LED, thru hole modular jack

Date: 5-30-18

Dimensions in mm Drawn By: Donna Mears