

τ	۵	н т	m	0







Keying Shown

02

F

S D

11

-

М

CHARACTERISTICS

BASIC SERIES:

SHELL SIZE: 11

PLATING : M = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ω

7

-Standard : Based on MIL-DTL-38999 Series III

\sim					
	-Shell Material	: Composite	┝		
	-Shell Plating	: Nickel	F		
	-Insulator	: Thermoplastic			
	-Contacts	: Copper Alloy	┢		
	-Seals & Grommet	: Silicon Elastomer	┢		
\sim	-Contact Plating	: Gold over copper Alloy 0.8µm minimum			
	-Durability	: 500 Mating cycles	L		
	-Delivered without Souriau contacts				
	-Temperature Range	65°C to +200°C			
	-Salt Spray	: 2000 hours			
	-Mass	: 10.3 g ± 10%			

8D 0

G

Dim	Nominal
Р	3.25±0.2
PP	4.93±0.2
R1	20.62
R2	18.26
S	26.2±0.3
V'	19.5+1.4/-0
W'	2.1/3.65
Ζ'	32 Max
V THREAD	M15x1-6g

m		0		A
S R1 R2				4
vn as example		LAYOUT SHOWN AS E	XAMPLE	3
Connector dimension Dim Nominal P 3.25±0.2 PP 4.93±0.2 R1 20.62 R2 18.26 S 26.2±0.3 V' 19.5+1.4/-0 W' 2.1/3.65 Z' 32 Max VV THREAD M15x1-6g		SOURIAU shall not be liable for and due to a use of the Products wh the Specifications issued by either or (professional recommendat Countr FR PN: 8D011N	hich does not comply with f the Parties or by a third party tion, technical notice.) Ty Jurisdiction & Control Lis Not Listed	t2
	ISS DATE Designed By: TITLE		CUSTOMER DRA	
L Delivered W/O Co ORIENTATI CONTACT TYPE : SOCKET(500 M		General linear Tolerances: ± NPRDS / PROJECT WWW.SOURIAU.COM 859 This document is the p SOURIAU it must not be repro communicated without		is the property of JRIAU e reproduced or
CONTACT LAYOUT	: 11-02 FORMAT A3 D	SOURIAU 8D011M0 C		A SHEET

F	Ŧ	۵		П	m	D		0	
		Contact Layout							Panel Cutou
4	. ×. (2)	+Y IB IA +Y +X 95 (2.4imm)					22 V	RUARE FLANGE RECEPTACLE (1 REAR MOUNTING	TYPE 0)
	Cont positi ID A B Shell Arrangement size no. 11 -2	tion X-axis Y-axis (mm) (mm) + .095 (2.41) +.000 (.00)	Contact location All				<u> </u>		ØA Dim
ω									ØA ØAA R1 ØT
								due to a use o the Specifications	ot be liable for any of the Products wh issued by either of onal recommendat
N									Countr FR I: 8D011N
_						IS	S DATE	6 First Release Latest modification Date:	
_							TITLE SCALE NA		General linear Tolerances: ±
						F	OURIAL DRMAT A3	WWW.	SOURIAU.C SOURIAU 8D011M(
L	Н	G		F	E	D	· [С	

