
-		 	_	
_	دی	 111	0	0







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 13

PLATING : M = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ယ

 \sim

-Standard : Based on MIL-DTL-38999 Series III

-Shell Material : Composite : Nickel -Shell Plating -Insulator : Thermoplastic -Contacts : Copper Alloy -Seals & Grommet : Silicon Elastomer -Contact Plating : Gold over copper Alloy $0.8 \mu m$ minimum -Durability : 500 Mating cycles -Delivered with Souriau contacts and Accessories : -65°C to +200°C -Temperature Range : 2000 hours -Salt Spray -Mass : 18.3 g ± 10%

8D 0

G

13

Μ

98

В


F

А

Dim	Nominal
Р	3.25±0.2
PP	4.93±0.2
R1	23.01
R2	20.62
S	28.6±0.3
V'	19.5+1.4/-0
W'	2.1/3.65
Z'	32 Max
/V THREAD	M18x1-6g

Е

SOURIAU shall not be liable for due to a use of the Products the Specifications issued by either (professional recomment



					1
	Φ		A		
1					4
s exa	AMPLE				3
whic	non-conformit h does not co he Parties or t	mply with	ty		
	on, technical n				
untry FR	Jurisd	liction & Cont Not Listed	trol List		2
3M	и98BA				
		CUSTOME	R DRAWING	MOD N°	
site	e Receptacle 8D series				
ar	NPRDS / PROJECT				
			59		1
J.CC	COM This document is the property of SOURIAU it must not be reproduced or communicated without permission				
	DRG N°			SHEET	
M9	8BA-C	I		1/2	J
	В		A		

		۵	ار (m	D	0	
		Contact Layout					Panel Cutout
4	د.	$ \begin{pmatrix} \bullet & \bullet \\ \bullet$			- 	SQUARE FLANGE RECEPTACLE (REAR MOUNTING R1	
	Contro position A B C C D C C D F F G G H J J K	n D (mm) (mm) +.000 (0.00) +.195 (4.95) +.125 (3.18) +.150 (3.81) +.123 (4.90) +.030 (0.76) 143 (4.90) +.030 (2.67) +.000 (0.00) 135 (3.43) 164 (4.17) 105 (2.67) 193 (4.90) +.030 (0.76) 125 (3.18) +.150 (3.81) +.026 (1.65) 015 (0.38)			₩ ₩		
ى نى	Shell Arrangement N size no. cc	065 (1.65) 015 (0.38) umber of ntacts Size contacts Contact rating Supersedes 10 20 I All MS20051-86					Dim ØA ØAA R1 ØT
						due to a use the Specifications	not be liable for any of the Products whi issued by either of onal recommendati
N							Country FR
						Р	N: 8D013N
	-				A 15-10-201 ISS DATE Designed By:	L6 First Release Latest modificatio Date:	n - by
					TITLE		Composite
<u> </u>					SCALE NA		General linear Tolerances: ±
					SOURIAL	J www.	SOURIAU.C
					FORMAT A3		SOURIAU 8D013M9
	Н	G	F	E	D	С	

