

SPECIFICATION:


BACKSHELL: ZINC, NICKEL PLATED,
COPPER UNDER PLATE
HOUSING SCREW: STEEL, ZINC PLATED
COMPRESSION INSERT: ABS, UL94-HB
OPERATING TEMPERATURE: -40°C TO +120°C

BACKSHELL KIT INCLUDES:

- (2) BACKSHELL HALVES
- (2) MOUNTING SCREWS
- (1) PLASTIC INSERTS TREE (4-SETS)
DIAMETERS: 0.157 [4.00], 0.167 [5.00], 0.276 [7.00], 0.354 [9.00]

*NORCOMP RECOMMENDS PURCHASING OUR SLIDE LOCK HARDWARE.
MUST BE PURCHASED SEPARATELY.

DIMENSIONS (in/mm)					
No. OF PINS	A	B	C	D	E
09	1.429	0.571	0.984	1.220	0.512
	36.30	14.50	24.99	31.00	13.00
15	1.587	0.571	1.312	1.555	0.512
	40.30	14.50	33.32	39.50	13.00
25	1.587	0.571	1.852	2.094	0.512
	40.30	14.50	47.04	53.20	13.00
37	1.587	0.571	2.500	2.744	0.512
	40.30	14.50	63.50	69.70	13.00



RoHS COMPLIANT

UNITS = inch [mm]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
C. SMITH
DATE:
03/30/2007

NorComp

SCALE: NTS	SHEET 1	OF 1	REV 3
DWG NO.			954-YYY-030R121