

MATERIAL:

BACKSHELL:

ZINC ALLOY

ZINC ALLOY


COVER:

MOUNTING SCREWS: STEEL, NICKEL PLATED

HOUSING SCREWS: GROUNDING SCREW: STEEL, ZINC PLATED

STEEL, ZINC PLATED


CABLE SLOT COVER: ZINC ALLOY OPERATING TEMP: -55°C TO +90°C



BACKSHELL KIT INCLUDES:

- (1) BACKSHELL
- (1) BACKSHELL COVER
- (2) MOUNTING SCREWS (#4-40)
- (4) HOUSING SCREWS (M2.5x0.45)
- (1) GROUNDING SCREW (M2.5x0.45)
- (2) CABLE SLOT COVER

**SEE PAGE 2 FOR CABLE CLAMPS



Mounting screw(s) shown to the left will not mate with any NorComp current hardware options. Please refer to NorComp 975M Series product page for slide lock hardware options (purchased separately).


UNITS = inch [mm]


DO NOT SCALE FROM DRAWING





DWG NO.	□ 075N/	IN5	<u></u>	30R121	
NTS		1		2	3
SCALE:	SHEET		OF		REV


CABLE CLAMPS ORDERED SEPARATELY














P/N **955-50-SR-8-10** CABLE RANGE = 0.315 - 0.394 P/N **955-50-SR-11-14** CABLE RANGE = 0.433 - 0.551 P/N **955-50-SR-14-16** CABLE RANGE = 0.551 - 0.630

ROHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE
OF ASSISTANCE OF MARKETING OF MARKETING

DRAWN:

M. SIGMON

DATE: 01/14/2014

NorComp

UNITS = inch

DO NOT SCALE FROM DRAWING

SCALE: SHEET OF REV

NTS 2 2 3

DWG NO. 975M050-030R121