

## 940 Extension

**speedtec** - ready

8-pin
EMC - Shielding
Earth-to-Housing Connection according to VDE 0627
Anti-vibration o-ring

## **Technical Data**

number of pins 8
power 4 (3+PE)
signal 4
temperature range -20 °C to 130 °C

temperature range  $-20 \, ^{\circ}\text{C}$  to  $130 \, ^{\circ}\text{C}$  clamping range  $\emptyset$  9.0 mm to  $\emptyset$  16.0 mm protection type when connected IP 66/67

 Electrical Data
 power
 signal

 rated current
 max. 75 A\*
 max. 30 A\*

 rated voltage
 630V (AC/DC)
 250 V (AC/DC)

 rated insulation voltage (L-L)
 6000 V
 4000 V

mating cycles 500

## Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3 over voltage category III max. height for operation 2000 m

## Material

housing zinc diecast / nickel plated insulation insert PA 6.6 mod., UL 94/V0 seals FKM clamp ring zinc diecast / nickel plated

Contacts (not part of product contents)

Tools (not part of product contents)

C KU A 268 NN 00 44 0051 000 C K A 268 N 00 44 0051 000



Contact Arrangement mating view



© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mall: intercontec@te.com Web: www.intercontec.biz



