

BU-P6383-02

(Red and Black Pair of Shrouded 4mm Banana Jack with Insulators)



- Used on stranded wire from 18 to 22 AWG with an insulator diameter from 0.06" to 0.15".
- Attach to wire with available crimp tools or by soldering.
- Provides safe and secure connections to 4mm shrouded banana jacks recessed for shrouded plugs.
- Compatible with most digital multimeters (Fluke, Wavetek, Agilent, Amprobe, Greenlee and others).
- Material:
 - o Banana Jack Nickel plated Brass
 - Insulation Santoprene (Thermoplastic Elastomer)
- Ratings:
 - o Hands free testing up to 1,500 V Max.
 - Operating Voltage: 300V Cat II (Handheld)
 - o Current: 15 Amps
 - Operating Temperature: -20°F (-29°C) to 275°F (135°C)
- RoHS 3 Compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524

<u>Assembly Instructions:</u> (Wire Not Included)



- 1. Slide Insulator over wire
- 2. Crimp/Solder wire to Banana Plug
- 3. Pull wire and slide insulator over banana plug
- 4. Insulator will lock into place once you have pulled it far enough over the plug.

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524