


Date	SYM	REVISION RECORD	AUTH	DR.	CK.
03/08/13	A	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	
06/02/17	B	DIM. 2.05 WAS 2.00	T.B.	B.S.	
6/02/17	F	DIM. 2.05 WAS 2.00	T.B.	B.S.	





**SPECIFICATION:**


**1. MATERIAL:**

HOUSING : BLACK POLYPROPYLENE  
 FLAMMABILITY RATING -UL94-HB, UL FILE NO. E216959  
 TEMPERATURE RANGE: -10°C to +100°C  
 RIVETS: BRASS, NICKLE PLTD.  
 9 VOLT SNAPS: BRASS, NICKEL PLATED  
 SPRING: SPRING STEEL, NICKLE PLTD.  
 CONTACT RESISTANCE: UNDER 50mΩ FOR +/- CONTACTS PER  
 EIA-540J000  
 ROHS 2 COMPLIANT

**MOUNTING INSTRUCTION:**

USE 2-56 MACHINE SCREWS OR EYELETS 0.089" OD  
 BY 0.15" FLANGE STIMPSON GS-3 SERIES OR EQUIVALENT.  
 ALSO ADHESIVES AND DOUBLE SIDED TAPES WORK WELL.



Tolerance (Except as noted)	 <b>Memory Protection Devices, Inc</b> 200 Broad Hollow Road, Farmingdale, New York 11735	Scale 1=1	Drawn By B.S.
			Approved By T.B.
decimal ±.020 (.5)	Title FOUR "C" CELL HOLDER WITH SNAP FASTENERS	Date 6/02/17	Drawing Number BH4CSF
Fractional ± .030 (.8)			
Angular ± 3°			