

BU-P6738

(BNC T-connector: Female, Female, Female)



- The BU-P6738 is a female-female-female BNC T-connector.
- Overall length 1.28" (32.6mm)

Material: Body Nickel-plated brass

Contacts Gold-plated Beryllium Copper

Insulator PTFE

• Rating: Impedance 75 Ohms

Temperature -50°C to 150°C

• RoHS 3 compliant

Toll Free: 800.955.2629

Phone: 330.780.2525

Fax: 330.780.2524