


CT1210LSCF Series

From 0.47 μH to 680 μH



CHARACTERISTICS

Description: SMD ferrite core wire-wound chip inductor.

Applications: LC resonant circuits such as oscillator and signal generators, impedance matching, circuit isolation, RF filters, disk drives and computer peripherals, audio and video equipment, TV, radio and telecommunication equipment.

Operating Temperature: -25°C to +85°C

Inductance Tolerance: $\pm 5\%$ & $\pm 10\%$

Testing: Inductance and Q are tested on an HP4285A at specified frequency.

Packaging: Tape & Reel.

Miscellaneous: RoHS Compliant.

Marking: Parts are marked with color dots in nano Henries.

Example: 10 μH = 10000nH ← marking would be Brown, Black, Orange(103).

Additional Information: Additional electrical & physical information available upon request

Samples available. See website for ordering information.

SPECIFICATIONS


Please specify tolerance code when ordering.

CT1210LSCF-1R0_ ← J = $\pm 5\%$, K = $\pm 10\%$

Part Number	Inductance (μH)	L Test Freq. (MHz)	Q Fact. Min.	Q Test Freq. (MHz)	SRF Min. (MHz)	DCR $\pm 30\%$ (Ω)	Rated DC (mA)
CT1210LSCF-R47_	0.47	25.2	40	25.2	450	0.07	1800
CT1210LSCF-1R0_	1.0	7.96	20	7.96	100	0.08	1500
CT1210LSCF-1R5_	1.5	7.96	20	7.96	80	0.11	1125
CT1210LSCF-1R8_	1.8	7.96	20	7.96	70	0.13	970
CT1210LSCF-2R2_	2.2	7.96	20	7.96	68	0.13	970
CT1210LSCF-2R7_	2.7	7.96	20	7.96	62	0.15	900
CT1210LSCF-3R3_	3.3	7.96	20	7.96	54	0.16	837
CT1210LSCF-4R7_	4.7	7.96	20	7.96	43	0.20	675
CT1210LSCF-5R6_	5.6	7.96	20	7.96	36	0.26	620
CT1210LSCF-6R8_	6.8	7.96	20	7.96	33	0.27	600
CT1210LSCF-8R2_	8.2	7.96	15	7.96	28	0.33	570
CT1210LSCF-100_	10	2.52	15	2.52	28	0.36	520
CT1210LSCF-150_	15	2.52	15	2.52	19	0.56	480
CT1210LSCF-180_	18	2.52	15	2.52	17	0.67	330
CT1210LSCF-220_	22	2.52	15	2.52	16	0.77	310
CT1210LSCF-270_	27	2.52	15	2.52	13	1.00	280
CT1210LSCF-330_	33	2.52	15	2.52	12	1.10	270
CT1210LSCF-470_	47	2.52	15	2.52	10	1.64	210
CT1210LSCF-680_	68	2.52	15	2.52	9	2.8	189
CT1210LSCF-101_	100	0.796	15	0.796	6	3.7	145
CT1210LSCF-151_	150	0.796	15	0.796	5	6.1	120
CT1210LSCF-181_	180	0.796	15	0.796	4	8.0	105
CT1210LSCF-221_	220	0.796	15	0.796	4	8.4	100
CT1210LSCF-331_	330	0.796	15	0.796	3.5	12	80
CT1210LSCF-471_	470	0.796	15	0.796	2.8	22	75
CT1210LSCF-681_	680	0.796	15	0.796	2	28	65

PHYSICAL DIMENSIONS

Size	A Max.	B Max.	C Max.	D	E	F
mm	3.70	2.90	2.6	0.51	0.51	1.52
inches	0.146	0.114	0.102	0.019	0.019	0.060



PAD LAYOUT

