

615915 Receptacle angled rotatable

24-pin flange mount /Flange 25x25

Technical Data

 number of pins
 24

 pow./sign.
 4 (3+PE) + 3

 pow./sign.
 12+5

 temperature range
 -20 °C to 130 °C

 protection type
 when connected IP 66/67

 Electrical Data
 pow./sign.
 pow./sign.

 rated current
 max. 14 / 5 A*
 max. 14* / 3.6 A*

 rated voltage
 63V (AC/DC)
 630 V / 63 V (AC/DC)

 rated insulation voltage (L-L)
 1500 V
 6000 / 1500 V

mating cycles 500

Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree 3 over voltage category III max. height for operation 2000 m

Material

housing zinc diecast / nickel plated insulation insert PBT, PA, UL 94/V0

Contacts (not part of product contents)

Tools (not part of product contents)

E ED A 103 NN 00 00 0001 000 E G A 103 N 00 00 0001 000









© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.

While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz

