

# FFA.1E.250.CTAC50

### SUMMARY

# Wires

Coax 1



Image is for illustrative purpose only

1E Series

Male solder Coaxial Termination type

IP rating 68 mated (mating interface)

0.00 - 0.00 AWG wire size Cable Ø 4.60 - 5.00 mm

Status Active

Matching parts ERA.1E.250.CTL **Download** 

Request a quote

Catalog

### **TECHNICAL DETAILS**

#### **Mechanics**

Shell Style/Model FFA\*: Straight plug, cable collet

Keying Circular, male

Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE **Housing Material** 

AMS QQ N 290] brass mid pieces

Weight 23.80 g

**Performance** 

Configuration 1E.250: 1 Coax (50 Ohm)

Insulator T: PTFE **Rated Current** 12 Amps

### **Specifications**

Contact Type: Coaxial 50 Ohm (Solder)

Contact Dia.: 0.9 mm (0.035in) Bucket Dia.: 1 mm (0.039in) Vtest: 3000 V (AC), 4200 V (DC)

Impedance: 50 Ohm VSWR: 1.01 + 0.23 \* f/GHz

Cable type: RG 178 B/U, RG 196 A/U, RG 188 A/U, RG 316 B/U, RG 174 A/U, HF-2114, RG 122 /U

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


### **Others**

Endurance (Shell): 5000 mating cycles Temp (min / max): -55°C / +200°C

Humidity (max): <=95% [at 60 deg C /140 F]

Vibration: 15 g [10 Hz - 2000 Hz] Shock Resistance: 100 g [ 6 ms] Climatical Category: 50/175/21 Shielding (min): 95 dB (10 MHz) Shielding (min): 80 dB (1 GHz) Salt Spray Corrosion: >1000 hr

## **DRAWINGS**



#### **Dimensions**

	А	L	М	S2
mm.	13	42	28	9
in.	0,51	1,65	1,10	0,35

# **RECOMMENDED BY LEMO**

### **Tools**

Spanner wrench: DCD.1E.ZZZ.PA090
Caps: BFA.1E.100.NAS

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

### **Cables**

158480	PUR	Black	
158490	PVC	Black	
CCX.50.088.292495N	PVC	Black	
CCX.50.RG5.8CU50N	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.