



Part Number:		DRAWN	F /20 /2010
ירכיםז	3220-1	CJ	5/20/2019
17233.		CHECKED	5/21/2019
		C.H.	5/21/2019
escription:	Indicator	APPROVED	F/21/2010
Plezo .		C.E.	5/21/2019

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View



## Side View



## **Bottom View**



Additional considerations can be found at www.dbunlimitedco.com/technical-articles.

Items	Specifications	Conditions					
Min. Sound Pressure Level	90	dB (@ 10cm)	1				
Tone	Single						
Resonant Frequency	3,300	Hz					
Rated Voltage	220	VAC	REVISION HISTORY				
Voltage Range	30 ~ 264	VAC	REV	DESCRIPTION	DATE	APPROVED	
Max. Rated Current	5	mA		Released from Engineering	10/21/2013	J.S.	
Storage Temperature	-30 ~ +70	°C	1	Updated drawing template, pin length tolerance	5/21/2019	C.E.	
Operating Temperature	-20 ~ +60	°C	NOTES				
Connection Method	PC Pins		All dimensions are in mm unless otherwise noted				
Mount Type	Thru Hole		2) All tolerances are ± 0.5 mm unless otherwise noted				
Housing Material	ABS		3) All parts meet RoHS				
Weight	0	n	4) Subject to change or redrawn without notice				