

Specifications			Notes		Revision History					
Description	Value	Unit	Notes		Version		Description		Date	Approved
Technology	Piezo		1) All dimensions are in mm	1	Released from Engineering			10/21/2013	J.S	
Resonant Frequency	2,900	(Hz)	2) All parts meet RoHS							
Rated Voltage	24	(V)								
SPL @ 10cm	95	(dBA)								
Tone	Single									
Mount Type	Panel									
Voltage Range	1~28	(V)								
Max Rated Current	15	(mA)								
Housing Material	NYLON				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-20 ~ +60	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-20 ~ +60	°C		Piezo Indicator	-	IP422924-1				
Weight	18	(g)		Fiezo indicator		IP422924-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.