


Pin	A	B	C
2	1.25	7.50	
3	2.50	8.75	
4	3.75	10.00	2.50
5	5.00	11.25	3.75
6	6.25	12.50	5.00
7	7.50	13.75	6.25
8	8.75	15.00	7.50
9	10.00	16.25	8.75
10	11.25	17.50	10.00
11	12.50	18.75	11.25
12	13.75	20.00	12.50
13	15.00	21.25	13.75
14	16.25	22.50	15.00
15	17.50	23.75	16.25
16	18.75	25.00	17.50



技术参数
 间距: 1.25
 温度范围: -25~+85°C
 额定电压: 125V AC, DC
 额定电流: 1.0A AC, DC
 接触电阻: 20mΩ
 绝缘电阻: 100MΩ
 耐压: 500V AC/minute

线性公差 / General Tolerance		标记		变更内容		签名		年月日	
X	±0.2								
X.X	±0.1								
X.XX	±0.05								
角度公差 / Angle Tolerance									
X°	±5.0°								
X.X°	±3.0°								
X.XX°	±1.0°								
视角 / Projection									
		审核							
		工艺				批准			

材料 / Material		
①塑座: LCP 本色		
②接触针: 黄铜 (镀锡)		
③焊片: 黄铜 (镀锡)		
阶段标记	版本	比例
	2.0	1:1
共 1 张		第 1 张

品名 / ProduceName
MX1.25 卧贴

 型号 / Model
BX-MX1.25-n*PWT