



CONFIGURATION DIMENSION

SIZE	DN	D	L	H	W
1/2"	15	15	62.5	50	98
3/4"	20	20	72	56	102
1"	25	25	82.5	63	110
1 1/4"	32	32	96	75	125
1 1/2"	40	38	106	86	156
2"	50	49	128	92	160
2 1/2"	65	65	163	120	215
3"	80	78	185	135	215
4"	100	100	235	155	310

MAIN PARTS AND MATERIALS

序列	名称	材质	序列	名称	材质
1	阀体 SEAT	CF8/CF8M	8	压盖 GLAND	CF8
2	球体 BALL	CF8/CF8M	9	手柄 HANDLE	201/CF8/CF8M
3	阀盖 BONNET	CF8/CF8M	10	Spring Washer	CF8
4	螺柱 NUT	CF8	11	螺母 NUT	CF8
5	垫片 GAKDET	PTFE	12	阀杆 STEM	CF8/CF8M
6	阀杆垫圈 STEM WASHER	PTFE	13	Spring Washer	CF8
7	填料 PACHING	PTFE	14	螺母 NUT	CF8

1 螺纹连接标准/PIPTHREADINACCORDANCENPTBSPTDIN2999RC

2 主体精密铸造/INVESTMENTCASTINGBODY

3 工作压力/WORKINGPRESSURE:20K (PN20)w.0.G

4 工作温度范围-30至100

5 压力试验标准/PRESSUREANDTESTSTANDARD:AP1598GB/T139271S05208

总装图

Q11-3PC 中型球阀

SIZE 1/4"~4" (DN8~DN100)

MJ-Q11-QTJ3