








7	8	9
标记	次数	更改单号
签名	日期	



SPECIFICATION (技术要求)

1. Operating Temperature(环境温度): -25℃~85℃
2. Voltage Rating(额定电压): 50V AC/DC
3. Current Rating(额定电流): 0.5A
4. Contact Resistance(接触电阻): 30mΩ
5. Insulation Resistance(绝缘电阻): 100MΩ
6. Dielectric Withstanding Voltage(耐电压): 500V AC Min
7. Insertion/Withdrawal Force(插拔力): 3-50N
8. Life Time(mating cycles)寿命: >1000 Cycles
9. All Material Must be Comply With RoHS.  
(此部品所有材料均符合RoHS要求.)



5	接触片	1	磷铜 t=0.2	镀铜>2um
4	拉簧套	1	SPCC t=0.3	镀锌>2um
3	支架	1	SPCC t=0.5	镀铜>2um
2	插芯	1	磷铜 t=0.3	镀铜>2um
1	垫圈	1	PPS	棕色
No.	零件名称 Part Name	数量Qty	材料 Material	镀层及颜色 Plating/Color

GENERAL TOLERANCES		DIMENSION:		PART NAME	射频频插座	DRAWING NO			SHEET
.XX±0.20		X±0.40				PART NO.	HC-PBZ-I041	PROJECTION	SCALE
.X±0.30		ANGULAR: ±2'		CUSTOMER NAME	mm				
DRAWN						CUSTOMER P/N	深圳市虹成电子有限公司		
CHECKED									
APPROVED									