

0 to 70 dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 6 GHz



RF Step Attenuators Technical Data Sheet

PE7440-70

Features

- 1 dB steps from 0 to 70 dB Attenuation
- Rotary Dial Control
- SMA Female Connectors

- · -20°C to +85°C Operating Temperature
- · ±1.5 dB Typical Attenuation Accuracy

Applications

Instrumentation

- Prototyping and Characterization
- Precision Measurements
- · Production Systems

Description

The PE7440-70 is a Step Attenuator that has 70 dB of total attenuation with 1 dB step size and rotary dial design across a frequency range from DC to 6 GHz. The design is tried and true technology that offers exceptional performance characteristics that include 1.8 dB maximum insertion loss, and a maximum VSWR of 1.55:1 at 6 GHz. The design also features excellent attenuation accuracy with ±1.5 dB typical at 6 GHz. The Brass package has SMA Female connectors, and operates within the temperature range of -20°C to 85°C.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
Insertion Loss			1.8	dB
Attenuation Value		0 to 70		dB
Step Size		1		dB
Step Type		Rotary		
Input Power (CW)			2	Watts
Input Power, Peak			100	Watts
5μs Pulse Width,2% DutyCycle				
VSWR			1.55:1	

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Range	DC to 6					GHz
Attenuation Accuracy	1.5					dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 0 to 70 dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 6 GHz PE7440-70

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com



0 to 70 dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 6 GHz



RF Step Attenuators Technical Data Sheet

PE7440-70

Mechanical Specifications

Size

 Length
 4.724 in [119.99 mm]

 Width
 1.181 in [30 mm]

 Height
 2.098 in [53.29 mm]

 Weight
 0.05 lbs [22.68 g]

Connectors

Description	Connector 1	Connector 2		
Туре	SMA Female	SMA Female		
Contact Material and Plating	Beryllium Copper, Gold			
Body Material and Plating	Brass, Nickel	Brass, Nickel		
body Waterial and Flatting	DIASS, NICKEI	Diass, Nickei		

Environmental Specifications

Temperature

Operating Range -20 to 85 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

0 to 70 dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 6 GHz from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 0 to 70 dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 6 GHz PE7440-70

URL: https://www.pasternack.com/70db-step-sma-female-sma-female-2-watts-attenuator-pe7440-70-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com

PE7440-70 CAD Drawing

0 to 70 dB Rotary Step Attenuator, SMA Female to SMA Female With 1 dB Step Rated to 2 Watts Up to 6 GHz

