



**NOTES:**

1. METALSHELLS.STELL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. FRAME: STEEL; NICKEL PLATED
4. FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
5. RIVETED INSERT: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
6. COLLAR: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
7. CONNECTOR IS PART MARKED: DSS3XSXXB01X CONEC ABC

Directive 2002/95/EC  
„RoHS“  
Compliant

|   |   |
|---|---|
| APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL | APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL |
| CUSTOMER APPROVAL DATE:                                   |   |
| NAME:   | TITLE:  |
| COMPANY NAME:   |   |
| APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL | APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL |

|  |             |       |      |                           |                          |            |
|--|-------------|-------|------|---------------------------|--------------------------|------------|
| THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH<br><br>DO NOT ALTER CAD DRAWING BY HAND |             |       |      | tolerance                 |                          | dim. in mm |
|  |             |       |      | date                      | name                     |            |
|  |             |       |      | drawn                     | 19.06.07    Lehmenkühler |            |
|  |             |       |      | appd.                     | 19.06.07    Mickenbecker |            |
| norm   |             | d-old |      | <b>CONEC</b> <sup>®</sup> |                          |            |
| a  | Origin      |       |      |                           |                          |            |
| rev.   | description | date  | name |                           |                          |            |

|                       |             |  |
|-----------------------|-------------|--|
| scale: 2:1 (5:1)      |             | title:<br><b>D-SUB FEMALE</b><br>25pos. CRIMP STYLE<br>with frame, float for blind mating system |
| material: SEE NOTES   |             |  |
| dwg no:               | Inventor 10 | DIN-A3   |
| 16K1A2090             |             | sh: 1  |
| part no: DSS3XSXXB01X |             |  |