






50W 3.7-8.3GHZ 10DB DIRECTIONAL COUPLER

PAGE 1/2 ISSUE 09-12-19A SERIES COUPLER PART NUMBER R433663000

Scale 1:1







All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **123,8700** g







50W 3.7-8.3GHZ 10DB DIRECTIONAL COUPLER

PAGE 2/2	ISSUE 09-12-19A	SERIES COUPLER	PART NUMBER R433663000
-----------------	------------------------	-------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency operating range:	3.7 – 8.3 GHz
Impedance:	50 Ω
VSWR: - Main Line	1.30 max.
- Coupled Line	1.30 max.
Nominal Coupling :	10 dB
Coupling Precision:	± 0.5 dB
Directivity:	18 dB mini
Insertion loss:	1 dB max.
Frequency Sensitivity:	± 0.3 dB
Average Power at 25°C	50W
Peak Power at 25°C	3000W

MECHANICAL CHARACTERISTICS

Connector type:	N female per MIL-C 39012
Coaxial Termination :	SMA, 50 Ω, 1W

ENVIRONMENTAL CHARACTERISTICS

Operating temperature :	-25°C / +85°C
Storage temperature :	-40°C / +100°C