
THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO RF INDUSTRIES, ANY UNAUTHORIZED USE OF THIS DRAWING IS EXPRESSLY PROHIBITED WITHOUT WRITTEN PERMISSION FROM RF INDUSTRIES.

ANY VIOLATION IS PUNISHABLE UNDER U.S. COPYRIGHT LAWS.

ALL DIMENSIONS ARE REFERENCE ONLY

PAR	RFB-1134	RFB-1134							
REV	DESCRIPTION	DWN	DATE	APPROVED					
_	ENGINEERING RELEASE	CZS	6/15/94	JDMc					
Α	UPDATED TO PTFE AND BRASS CONTACT MATRL	JDM	4/24/19	JDMc					
A1	CHANGED ZINC BODY TO BRASS MATRL	JDM	6/5/20	JDMc					
				·					



SPECIFICATIONS:

IMPEDANCE: 50 Ohms

FREQUENCY RANGE: 0-4 GHz

WORKING VOLTAGE: 500 V rms @ sea level TEMPERATURE RANGE: -65°C TO 165°C

1	BODY	1	BRASS	NICKEL, 80μ "	000494		Ū
2	INSULATOR	۵	PTFE				ı.
3	CONTACT	1	BRASS	GOLD, 3μ "	1		Ŀ
4	PRESS WASHER	1	BRASS	NICKEL, 80μ "	1		E
5					1		Ľ
6					1		ŀ
7					1		l
8							L
9							ı
10					DRAWN JDM	6/5/20	ı
11					CHECKED	0, 0, 20	ı
12					CHECKED		ı
13					ORJ DRAWN	2 (27 (22	ı
14					C. ZUNIGA	9/23/02	ı
#	DESCRIPTION	QTY	MATERIAL	FINISH	APPROVALS	DATE	ı

UNLESS OTHERWISE SPECIFIED:

- 1. REMOVE ALL BURRS
- 2. BREAK ALL CORNERS & EDGES .005 R. MAX. 3. CHAMFER 1ST & LAST THREADS 45
- 4. SURFACE ROUGHNESS 63 FINISH MIL-STD-10 5. DIAMETERS ON COMMON CENTERS TO BE
- CONCENTRIC WITHIN .002 T.I.R.
 6. ALL DIMENSIONS ARE AFTER PLATING.

DIMENSIONS ARE IN INCHES AND [MILLIMETERS]

UNLESS OTHERWISE NOTED TOLERANCES ARE:

DECIMALS .XXX±.003 [.08] .XX±.005 [.13]

DIAMETER
.XXX±.001 [.03]
.XX±.003 [.08]



7610 MIRAMAR RD SAN DIEGO,CA 92126 (858) 549-6340 (858) 549-6345 FAX

BNC JACK TO JACK

ADAPTER

SIZE CABLE GROUP DWG NO. REV A 1

SCALE: NTS CAD FILE OUTLINE SHEET 1 OF 1