



		1	
Part Number:		DRAWN	10/21/2013
エレンン	3412-1	A.B.	
IP233		CHECKED	10/21/2013
		C.E.	
Description:		APPROVED	10/21/2013
Piezo I	ndicator	J.S.	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


## Top View



## Side View



## **Bottom View**



A -	Items	Specifications	Conditions				
	Sound Pressure Level	90	dB (@ 10cm)				
	Tone	Single		1			
	Resonant Frequency	3,400 ± 400	Hz	REVISION HISTORY			
	Rated Voltage	12	V	REV	DESCRIPTION	DATE	APPROVED
	Voltage Range	3 ~ 20	V		Released from Engineering	10/21/2013	J.S.
	Max. Rated Current	15	mA	1	Show washtab, update temps, update to new template	7/5/2017	C.E.
	Storage Temperature	-40 ~ +85	°C	NOTES			
	Operating Temperature	-30 ~ +70	°C	All dimensions are in mm unless otherwise noted			
	Connection Method	PC Pins		2) All tolerances are ± 0.5 mm unless otherwise noted			
	Mount Type	Thru Hole		3) All parts meet RoHS			
	Housing Material	Noryl		4) Subject to change or redrawn without notice			
ı	Weight	4	n				