

Model H4700BZ3RCSFPM

Panel Mount Antenna

Key Features



Panel Mount Connector



Circular Polarization



Rugged Polycarbonate Radome



Low Profile



Electrical Specifications	H4700BZ3RCSFPM
Frequency Range, MHz	4400-5000
Gain, dBi	6 nominal
VSWR	2.0:1 Nominal1.2:1 typical
3 dB Bandwidth E/H degrees	65/65
Maximum Power, watts	25 W
Mounting	Panel Mount
Connector	SMA Female
Polarization	Right Hand Circular
Material	Brass Ground Plan and Element
Radome	Polycarbonate; Black



Mechanical Specifications	H4700BZ3RCSFPM
Vibration	Transportable equipment/vehicle mounting
Humidity	95% non-condensing
Operating Temperature	-40F to +140F
Storage Temperature	-40F to +140F