







APPROVED: \_\_\_\_\_  
 DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	9/12/16	
A		ADDED CRICUIT DIAGRAM	11/16/17	AY/RT
B		UPDATE SPEC.	3/27/18	AY/YC



SIM pin Assignment	
PIN#	Name
C1	VCC
C2	RST
C3	CLK
C5	GND
C6	VPP
C7	I/O



**SPECIFICATIONS:**

Material:  
 Insulation: Hi-Temp Thermoplastic, UL94V-0, Color: Black  
 Contact: Copper Alloy  
 Shell: Stainless, Nickel plated, 1u" Gold over Nickel underplate on contact area  
 Plating:  
 Gold flash over Nickel underplate on contact area  
 Electrical:  
 Voltage rating: 10V DC  
 Current rating: 0.5 mA AC/DC max  
 Contact resistance: 100 mohms Max.  
 Insulation resistance: 1,000 Mohms min @ 500 VDC  
 Temperature Rating:  
 Operating temperature: -40°C to +85°C  
 Environmental:  
 Lead free, RoHS compliant



■ CIRCUIT TRACE KEEP OUT AREA  
 ▨ SMT SOLDER AREA

PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED  
 ALL DIMENSIONS ARE INCHES [MM]  
 TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

**ADAM TECH**  
 INTERCONNECTS  
 909 Rahway Avenue,  
 Union, NJ 07083  
 Phone: 908-687-5000  
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	AY	9/12/16
CHECKED	SC	9/12/16
APPROVED		

TITLE			
MICRO SIM CARD CONNECTOR, PUSH-PUSH TYPE, 6 PIN, SEL-GOLD PLATED, TAPE & REEL			
SIZE	PART NO.	REV.	
X	MSCCP-A1-06-SG-SW-T/R	B	
REF: S00275T	SCALE: NTS	SHEET 1 OF 1	