## by Fit-N

### Cat6/Cat5e 110 Style Punch Down Keystone Jack - Red, 25-Pack, TAA

#### MODEL NUMBER: N238-025-RD



#### Description

This Cat6/Cat5e 110-Style Punch-Down Keystone Jack provides maximum flexibility for any UTP Ethernet environment. Ideal for Cat5e cabling environments, the jack also meets UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test for Cat6 cabling installations. The uniquely patterned printed circuit board construction is designed to meet Cat6 250 MHz performance, and is fully compliant with EIA/TIA Cat6 connecting hardware specifications. With its compact casing, it fits into any conventional face plate, outlet box or panel. It also features dual-color-coded labeling made for both 568A and 568B (258A) wiring schemes.

UTP Cat6 22-24 AWG solid cable

#### Features

- 25-Pack
- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA Cat6 connecting hardware specifications
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes
- Compact casing fits into any conventional face plate, outlet box, or panel
- UL-certified ANSI/TIA/EIA-568-B.2-1 Permanent Link/Channel Identification Test
- Uniquely patterned, printed circuit board designed to meet Cat6 performances
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### **Specifications**

OVERVIEW	
UPC Code	037332187857
Technology	Cat5/5e; Cat6
PHYSICAL	

#### Highlights

- 25-Pack
- Use in Cat6 or Cat5e installations
- Compliant with EIA/TIA CAT6 connecting hardware specifications.
- Dual-color coded labeling made for both 568A & 568B (258A) wiring schemes.
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

#### Package Includes

- Cat6/Cat5e 110 Punch Down Keystone Jack - Red, 25-Pack
- Termination Caps (x25)

# TRIPP-LITE

Color	Red	
Connector Color	Red	
Shipping Dimensions (hwd / in.)	7.01 x 7.87 x 0.50	
Shipping Dimensions (hwd / cm)	17.81 x 19.99 x 1.27	
Shipping Weight (lbs.)	0.49	
Shipping Weight (kg)	0.22	
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000	
CONNECTIONS		
Number of Ports	1	
Side A - Connector 1	RJ45 (FEMALE)	
Side B - Connector 1	110 IDC	
STANDARDS & COMPLIANCE		
Product Certifications	UL 1863; UL 2043	
Product Compliance	RoHS; Trade Agreements Act (TAA)	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.