



Radiall 狐

SMA ATTENUATOR 1DB 12.4GHZ 2W

PAGE 1/2 ISSUE 24-08-15D SERIES ATTENUATOR PART NUMBER R411801119







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 2 OVER NICKEL 2
Female center contact Outer contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2
Insulator Gasket	PTFE SILICONE RUBBER	
Substrate Resistor	ALUMINA THIN FILM	
Others parts	-	-







PAGE 2/2 ISSUE 24-08-15D SERIES ATTENUATOR PART NUMBER R411801119

## **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4
V.S.W.R (≤)	1.20	1.25	1.30
Deviation(±dB)	0.30	0.40	0.50

Operating Frequency Range	DC - 12.4	GHz
Impedance	50	Ω
Nominal Attenuation	1	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


## MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	<b>4,7300</b> g		

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	<b>-55 /+125</b> °C
Storage temperature range	<b>-55 /+125</b> °C

#### Power derating Versus temperature



# SPECIFICATION

# OTHER CHARACTERISTICS