Part #: MALLORY Mallory Sonalert Products, Inc. **ZA016SDCT Sales Outline Drawing** Revision: E **Specifications:** Sound Level Category Soft Mode of Operation Continuous Voltage Rating 6 to 16 VDC Frequency 3900 ± 500 Hz Loudness @ 2 FT 65 to 75 dB(A) Typ. **Current Draw** 40mA MAX Housing Material 6/6 Nylon, Color: Black Storage Temperature -40° to +80° C **Operating Temperature** -30° to +65° C **Panel Mounting** Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole. Knurled Nut Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical) 28 g NEMA 3R,4X, & 12 Approved with use of included gasket. cUL Recognition cUL Recognized Please contact factory. Options cUL Recognized **ROHS Compliant Dimensions:** Inches (mm) 1.710 [43.44] 0.524 [13.31] 1.210 [30.74] Gasket M22 x 1.5 Thread <0.86 Maj. Dia.

Knurl nut