## MALLORY Mallory Sonalert Products,Inc. Part #: **ZA048SACT** Revision: **Sales Outline Drawing Specifications:** Sound Level Category Soft Mode of Operation Continuous Voltage Rating 28 to 48 VAC/DC 3900 ± 500 Hz Frequency Loudness @ 2 FT 65 to 75 dB(A) Typ. 40mA MAX **Current Draw** Housing Material 6/6 Nylon, Color: Black Storage Temperature -40° to +85° C **Operating Temperature** -30° to +85° C **Panel Mounting** Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole. Knurled Nut Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical) 28 q NEMA 3R,4X, & 12 Approved with use of included gasket. Options Please contact factory. **cUL** Recognized **ROHS Compliant Dimensions:** Inches (mm) 0.524 [13.31] 1.710 [43.44] 1.210 [30.74] Gasket M22 x 1.5 Thread <0.86 Maj. Dia.

Knurl nut