



Pre-assembled relay module PRS..., Screw connection, Consisting of: relay socket base, power contact relay, pluggable display/suppression module and holding clip, 4 CO contacts, Input voltage: 115 VAC

Kaufmännische Daten

Artikelnummer	<u>15733.2</u>
Artikelbezeichnung	PRSU 4G/115V AC
GTIN (EAN)	4044211138530
Packaging unit	1
Quantity unit	PC
Weight per piece (not including packaging)	55.4 g
Weight per piece (including packaging)	61.2 g
Unit of weight	G
Customs number	85364900
Country of origin	CN
Product description	Complete module

Technische Daten

Dimensions

Length	76 mm
Width	27.1 mm
Height TS 35 / 7.5 with BA	87 mm

Ratings

Rated voltage Un	115 VAC -
Overvoltage category	III
Contamination degree	3

Connection data

Connection principle	Screw connection
Wire cross-section single core (rigid), min.	0.2 mm ²
Wire cross-section single-core (rigid), max.	2.5 mm ²
Wire cross-section stranded, min.	0.2 mm ²
Wire cross-section stranded, max.	2.5 mm ²
Wire cross-section stranded with wire-end ferrules, min.	0.2 mm ²
Wire cross-section stranded with wire-end ferrules, max.	1.5 mm ²
Stripping length	8 mm
Torque	0.8 Nm

Input data

Drop-out voltage	34,5 VAC
Operating range	ab 92,0 VAC
Power consumption	1 W

Output data

Switching voltage / switching voltage max.	240 / 240 VAC
Continuous current max. / Inrush current max.	6 / 12 A
Contact configuration	4 CO contacts
Switching capacity, max.	1500 VA
Electrical lifespan (AC1)	1,5x10 ⁵
Mechanical lifespan	20x10 ⁶
Contact load, min.	120 mW
Bounce time at close of the NO/NC contact	6/8 ms

Technische Daten

Materials

Contact material	AgNi 90/10
Flammability class UL 94	V-0
Working temperature, min.	-25 °C
Working temperature, max.	70 °C

Further technical data

Degree of protection	IP20
Status display	✓
Insulation voltage coil/contact	2,5 kV
Insulation voltage contact/contact	1,2 kV
Test button	✓
Vibration resistance NO/NC	7/4 g
Pinning	2.8 (fast-on) mm
Coil and contact connections are separated	✓

Environmental Product Compliance


REACH Conform	yes
REACH Reference date	2023-06-14
REACH Candidate Substance Note	No
RoHS Conform	yes

Zulassungen

Standards and regulations

CE compliant	yes
--------------	-----

Medien



Zubehör

Cross-connector



External cross-connector insulated, for relay socket base PRS 4/6-pole, can be shortened, Voltage: 250 V, Current: 10 A

Artikelnummer	Artikelbezeichnung	GTIN (EAN)	VPE
<u>15778.2</u>	AQI/PRS/6 BK	4044211133993	20 ST

Screwdriver



Screwdriver with bare blade, Colour: Black-grey

Artikelnummer	Artikelbezeichnung	GTIN (EAN)	VPE
<u>1086.0</u>	SDB 0,6x3,5	4044211014797	1 ST

Relays



Plug-in industrial relays with power contacts, 4 CO contacts, Test button, Mechanical switching position indicator, Input voltage: 115 VAC

Artikelnummer	Artikelbezeichnung	GTIN (EAN)	VPE
<u>15257.2</u>	PRS 4/115V AC	4044211046835	1 ST

Holding clamp



Relay holding clip, With eject, Suitable for relay socket base PRS 4, for industrial relays

Artikelnummer	Artikelbezeichnung	GTIN (EAN)	VPE
<u>15140.2</u>	PRS C4	4044211046224	1 ST

Insert modules



Insertion module, Suitable for relay socket base PRS, LED red status display

Artikelnummer	Artikelbezeichnung	GTIN (EAN)	VPE
<u>15142.2</u>	PRS LED(RD) 230V AC	4044211046255	1 ST