
MALLORY Mallory Sonalert Products,Inc.	Part #:	SBT200PC
Sales Outline Drawing	Revision:	F

Specifications:	cUL Recognized as capable of meeting Medical Spec IEC60601-1-8 AMD2:2020	
Sound Level Category:	Loud	
Mode of Operation:	Medical Spec IEC60601-1-8	
Voltage Rating:	5, 30 Max	
Frequency:	150 to 4000 Hz	
Loudness @ 10cm:	85 to 95 dB(A) Typ.	
lpk Current*:	1.5mA at rated voltage	
Housing Material:	ABS 777D Plastic Resin, Black	
Storage Temperature:	-40° to +85° C	
Operating Temperature:	-30° to +65° C	
Weight Typical:	0.6 oz (17g)	
Options:	Please contact factory.	
Condition by wave solder (°C)	260 ± 5 within 5 sec	
Condition by hand solder (°C)	350 ± 20 within 5 sec	

Dimensions: Inches (mm) cUL Recognized ROHS Compliant

PATENT NUMBER: 7880593

Before Code Date: 1546 Not cUL Recognized After Code Date: 1547 cUL Recognized



4411 South High School Road, Indianapolis, Indiana 46241 U.S.A · Phone: (317) 612-1000 Fax: (317) 612-1010

tolerances:

±0.01 [±0.3] ±0.005 [±0.1]