Part #: MALLORY Mallory Sonalert Products, Inc. SCE028LD2VC3B **Sales Outline Drawing** Revision: Α **Specifications:** Sound Level Category: Medium Loud Soft Mode of Operation: Medium Pulse Medium Pulse Medium Pulse Pulse Rate (PPS): 5 65 to 75 dB(A) Typ. Loudness @ 2 FT: 85 to 95 dB(A) Typ. 75 to 85 dB(A) Typ. 2000 ± 500 Hz 2000 ± 500 Hz 2000 ± 500 Hz Frequency: T-BLOCK; BLUE WIRE T-BLOCK; YELLOW T-BLOCK ONLY Connection: TO (-) WIRE TO (-) Voltage Rating: 16 to 28 VDC 40mA MAX **Current Draw:** Housing Material: 6/6 Nylon, Color: Black Storage Temperature: -40° to +85° C -40° to +85° C Operating Temperature Panel Mounting: Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. Knurled Nut: Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical): 2.1 oz (60g) NEMA 3R,4X, & 12: Approved with use of ACC03. cUL Recognition: cUL Recognized Please contact factory. Options: **ROHS Compliant Dimensions:** Inches (mm) YELLOW-BLUE SONALERY Made in U.S.A. 1.210 1.240 APPROX. 6" LONG 24 AWG INSULATED 1 1/8-24 UNS 2A THD. -CONTROL WIRES FLEX. STRANDED KNURLED NUT -SOCKET (5mm Pin Spacing) PLUGGABLE SCREW 1.3 [33.0] Ref. TERMINAL BLOCK .375±.005 [9.53±.13]→ .47±.01 [11.94±.25] - .031±.005 [.79±.13] 1.90±.1 [48.26±2.54] ►