## MALLORY Mallory Sonalert Products, Inc. Part #: SCE028XD2MG7B **Sales Outline Drawing** Revision: D Specifications: Sound Level Category: Extra Loud Loud Mode of Operation: Continuous Ding Dong 2.0 - 1.6 kHz Pulse Rate (PPS): N/A 1.2 85 to 95 dB(A) Typ. Loudness @ 2 FT: 95 to 105 dB(A) Typ. 2000 ± 500 Hz 2000 ± 500 Hz Frequency: T-BLOCK: BLACK WIRE Connection: T-BLOCK ONLY TO (-) Voltage Rating: 16 to 28 VDC **Current Draw:** 40mA MAX Housing Material: 6/6 Nylon, Color: Black Storage Temperature: -40° to +85° C **Operating Temperature** -40° to +85° C Panel Mounting: Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. Knurled Nut: Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical): 2.1 oz (60g) NEMA 3R,4X, & 12: Approved with use of ACC03. cUL Recognition: cUL Recognized

