
Data sheet | Item number: 855-3001/125-003 Split-core current transformer; Primary rated current: 125 A; Secondary rated current: 1 A; Rated power: 0.2 VA; Accuracy class: 3



www.wago.com/855-3001/125-003



Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.



Item description

Short description:

WAGO's compact split-core current transformers are ideal for retrofitting existing systems. They are perfect for applications in which the current path must not be disrupted. The transformer's accuracy permits extremely precise current measurements. The split-core current transformers are capable of supplying the specified rated power at the end of the secondary cable. All transformers are supplied with color-coded cables. Two UV-resistant cable ties are also included for secure and easy mounting. **Features:**

- Current ratios from 125 A (primary side) and 1 A (secondary side)
- No measuring cable interruption
- Ideal for use in very confined spaces
- Rapid mounting
- For use around insulated cables up to 18 mm diameter
- Compact and hinged
- Color-coded connecting cable 3 m

Data

Technical data

Accuracy class	3
Primary rated current	125 A
Rated continuous thermal current I _{cth}	100 %
Rated short-time thermal current I _{th}	60 x I _N / 1 s
Rated surge current I _{dyn}	2.5 x I _{th}
Rated frequency	50 60 Hz
Secondary rated current	1A
Rated power S _r	0.2 VA

Safety and protection

Highest voltage for equipment U _m	AC 720 V _{rms}
Protection type	IP20
Test voltage	AC 3 kV; 50 Hz; 1 min

Subject to changes. Please also observe the further product documentation!

 WAGO Kontakttechnik GmbH & Co. KG
 Do you have any questions about our products?

 Hansastr. 27
 We are always happy to take your call at +49 (571) 887-44222.

 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169

 Email: info.de@wago.com | Web: www.wago.com
 Email: info.de@wago.com | Web: www.wago.com



Connection data

Feedthrough for measurement conductor	Ø 18 mm
Cable type	2 x 0.5 mm²; fine-stranded
Color code	brown = S1; blue = S2
Physical data	
Cable length	3 m
Mechanical data	
Mounting type	Split-core current transformer (suspended)
Material data	
Flammability class per UL94	V2
Weight	225 g
Environmental requirements Surrounding air temperature (operation)	-1055 °C
Surrounding air temperature (storage)	-2070 °C
Relative humidity	5 85 % (without condensation)
Operating altitude (max.)	2000 m
Standards and specifications	
Standards/Specifications	EN 61869-1 EN 61869-2
Commercial data	
PU (SPU)	1 Stück
Packaging type	box
Country of origin	NL
GTIN	4055143950732

85043180888

Downloads Documentation

Customs tariff number

Bid Text

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.

Data sheet | Item number: 855-3001/125-003

www.wago.com/855-3001/125-003



	docx 15.4 kB	Download
	xml 5.3 kB	Download
V 1.1.0 Jan 15, 2020	pdf 832.5 kB	Download
1.0.7.9 _{9S} Apr 8, 2021	exe 114.0 MB	Download
1.0.7.9 Apr 8, 2021	exe 30.0 MB	Download
	URL	Download
	Jan 15, 2020 1.0.7.9 PS Apr 8, 2021 1.0.7.9	V1.1.0 pdf Jan 15, 2020 832.5 kB 1.0.7.9 exe Apr 8, 2021 114.0 MB 1.0.7.9 exe Apr 8, 2021 30.0 MB

Installation Notes

Installation

Simple termination!

Quick and easy mounting!

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG Hansastr. 27 32423 Minden Phone: +49571 887-0 | Fax: +49571 887-169 Email: info.de@wago.com | Web: www.wago.com Do you have any questions about our products? We are always happy to take your call at +49 (571) 887-44222.