т	۵	п	m	0







LAYOUT SHOWN AS

Keying Shown as example

CHARACTERISTICS

ယ

 \sim

-Mass

Н

-Standard : Based on MIL-DTL-38999 Series III

Ť	-Shell Material	: Composite			
	-Shell Plating	: Olive drab Cadmium			
	-Insulator	: Thermoplastic			
	-Contacts	: Copper Alloy			
	-Seals & Grommet	: Silicon Elastomer			
	-Contact Plating	: Gold over copper Alloy 0.8µm minimum			
	-Durability	: 500 Mating cycles			
	-Delivered without Souriau contacts				
	-Temperature Range	65°C to +175°C			
	-Salt Spray	: 2000 hours			
1					

Connector dimension			
Dim	Nominal		
Р	3.25±0.2		
РР	4.93±0.2		
R1	23.01		
R2	20.62		
S	28.6±0.3		
۷'	19.5+1.4/-0		
W'	2.1/3.65		
Ζ'	32 Max		
VV THREAD	M18x1-6g		


Delivered W/O Contacts

CONTACT LAYOUT : 13-08


CONTACT TYPE : PIN(500 Matings)

Е

ORIENTATION : N







F

G

	Φ		A			
					4	
	AMPLE				3	
any non-conformity or damage which does not comply with or of the Parties or by a third party dation, technical notice.)						
Intry R	y Jurisdiction & Control List Not Listed				2	
3J08PNL						
				MOD N°		
		CUSTOME	R DRAWING			
	e Receptacle 8D series					
ar	NPRDS / PROJECT 859					
I.CC	.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission					
	UDRG N° SHEET					
108	BPNL-C		A	1/2	J	

		۵	ار (m		0
		Contact Layout				Panel Cutout
4	×	$ \begin{array}{c} & & & \\ & & & \\ & & & \\ & & & \\ & $			1	SQUARE FLANGE RECEPTACLE (TYPE 0) REAR MOUNTING
		D (mm) (mm) (mm) (mm) (mm) 3 +.065 (1.65) +.157 (3.99) 3 +.170 (4.32) +.000 (0.00) C +.120 (3.05) 120 (3.05) D 000 (0.00) 170 (4.32) E 120 (3.05) 120 (3.05) F 170 (4.32) +.000 (0.00) 3 065 (1.65) +.157 (3.99)			~ - ~	
ယ		mber of Size Service Contact Supersedes ntacts contacts rating location 8 20 I All MS20051-8				Dim ØA ØAA R1 ØT
						SOURIAU shall not be liable for any due to a use of the Products whi the Specifications issued by either of (professional recommendati
N						PN: 8D013J0
					A 14-10-20 ISS DATE Designed By:	16 First Release Latest modification - by Date:
_					TITLE SCALE NA	General linear Tolerances:
					SOURIA	
			_	- 1	FORMAT A3	SOURIAU 8D013J08
	Н	G	F	E	D	C

