

Φ		A				
11.01				4		
	/					
and the	1					
S EXAMPLE				3		
any non-conformi	ty or damage					
which does not co	iny non-conformity or damage which does not comply with of the Parties or by a third party					
	of the Parties or by a third party lation, technical notice.)					
intry Jurisc	liction & Contr Not Listed	ol List		2		
W90SNL						
UV JUJINL						
	CUSTOMER	DRAWING	MOD N°			
um Receptac	m Receptacle 8D series					
ar	NPRDS / I					
	85 This docu		perty of	1		
COM This document is the property of SOURIAU it must not be reproduced or						
	communicated without permission					
			SHEET 1/2			
V90SNL-C		A	1/2	J		
_						

	Ŧ	۵	н п	т		0	
		Contact Layout				Panel cutout	
4	<u>-x</u> s	$\begin{array}{c} \checkmark \cdot \mathbf{y} \\ \mathbf{W} \odot \odot \odot^{A} \otimes \mathbf{W} \\ \mathbf{W} \odot \odot \odot^{A} \otimes \mathbf{W} \\ \mathbf{W} \odot \odot \odot^{A} \otimes \mathbf{W} \\ \mathbf{W} \odot^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \\ \mathbf{W} \odot^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \\ \mathbf{W} \odot^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \\ \mathbf{W} \odot^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \otimes^{A} \\ \mathbf{W} \odot^{A} \otimes^{A} \otimes^{A$				JAM NUT RECEPTACLE (TYPE 7	
	Contact position Local (mm) A +.065 (1.65) B +.275 (6.99) C +.420 (10.67) D +.490 (12.45) E +.531 (13.49) F +.531 (13.49) G +.490 (12.45) H +.420 (10.67)	Y-axis (mm) Contact position ID X-axis (mm) Y-axis (mm) +.533 (13.54) a +.404 (10.26) +.125 (3.18) +.466 (11.84) b +.437 (11.10) +.000 (0.00) +.337 (15.66) c +.404 (10.26) +.125 (3.18) +.227 (5.77) d +.314 (7.98) 221 (5.61) +.093 (2.36) e +.245 (6.22) 337 (8.56) 033 (2.36) f +.138 (3.45) 424 (10.77) 337 (8.56) h 136 (3.45) 424 (10.77)				Ø	
ى س	$\begin{array}{c} J & +.275(6.99) \\ K & +.065(1.65) \\ L &065(1.65) \\ M &275(6.99) \\ N &420(10.67) \\ P &490(12.45) \\ R &531(13.49) \\ T &490(12.45) \\ U &420(10.67) \\ V &065(1.65) \\ X & +.136(3.45) \\ X & +.136(3.45) \\ Y & +.26(6.22) \\ Z & +.314(7.98) \\ \end{array}$	$\begin{array}{rrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrrr$				Dim Nom B 43.43+1 ØC 44.7+0	0/-0.25
	2	Size contacts Service rating Contact location Standard contact 8 see note) Twinax W. Z M39029/90-529 M39029/91-53 16 20 1 Y. X. Y. AA M39029/58-364 M39029/56-355 20 1 All others M39029/58-363 M39029/56-355	2			SOURIAU shall not be due to a use of the the Specifications issue (professional r	e Products whic d by either of t
N						PN: 8	Country FR BD725W
_					A 05-10-20 ISS DATE Designed By:	16 First Release Latest modification - by Date:	,
					SCALE		luminium eneral linear
_					NA SOURIA		^t olerances: ±
					FORMAT A3	SC	DURIAU 0725W9
	Н	G	F	E	D	C	

Β	A				
T		4			
L		3			
any non-conformit which does not co or of the Parties or b idation, technical n intry Jurisc R SW90SNL	mply with by a third party otice.) liction & Control List Not Listed	2			
	CUSTOMER DRAWING	10D N°			
um Receptacle 8D series					
ır	NPRDS / PROJECT 859 This document is the property	1			
I.COM it must not be reproduced or communicated without permission					
U DRG N° V90SNL-C		SHEET 2/2			
В	A				