



ANTENNA TECHNOLOGIES LIMITED COMPANY

Model ADP4700SBFSCTM

Dipole Omni

Key Features

- Monopole and dipole designs
- Excellent mechanical integrity and electrical performance
- Ruggedized construction for field durability
- Custom frequencies available
- Spring base and / or Fiberglass radome



Electrical Specifications	ADP4700SBFSCTM
Frequency Range, MHz	4400-5000 MHz
Impedance	50 ohm nominal
VSWR	<2.0:1
Gain	2dBi
Polarization	Vertical

Mechanical Specifications	ADP4700SBFSCTM
Connector Style	TNC Male
Material	Brass, Polyolefin Adhesive Lined
Operation Temp.	-20c to +65c
Storage Temp.	-30c to +75c