



P.C.B LAYOUT



1.3 : 轴套长度1.3mm

SCHEMATIC

12	PJ307D CONTACT CLIP	PBS	1	Ag CLAD
11	PJ307D SLIDER	NYLON	1	BLACK
10	PJ307D TERMINAL	BRASS	1	Ag PLATED
9	PJ307D BASE	PHENOLIC RESIN	1	YELLOW
8	PJ307D HOUSING	NYLON	1	BLACK
7	PJ307 AXIS GUIDE	BRASS	1	Ni/Au PLATED
6	PJ307E 5#SPRING	SUS	1	Ag PLATED
5	PJ307G 4#CURVE PIECE	BRASS	1	Ag PLATED
4	PJ307G 3#CURVE PIECE	BRASS	1	Ag PLATED
3	PJ307G 2#SPRING	PBS	1	Ag PLATED
2	PJ307 1#CONTACT FOOT	PBS	1	Ag PLATED
1	PJ307 CASE	PBT	1	BLACK
NO.	PART NAME	MATERIAL	QTY	FINISHING

TOLERANCE UNLESS SPECIFIED					
UP TO 5mm: ±0.1	ANGULAR	AO	2017.10.26	首次发行	GYW
ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS	BY APPD
TITLE:PHONE JACK		UNIT : MM	ROHS COMPLIANT	DWN	
MODEL:PJ-307A-1.3		SCALE: 3:1	CHK'D		
HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司		APPD			
		PRO.AGL:			REV :A0