

**Mechanical**



ACTUATION FORCE: 100 grams, 160 grams, 200 grams, 260 grams  
 LIFE EXPECTANCY: 100,000 operations.

**Electrical**

CONTACT RATING: 50 mA @ 12 V DC.  
 DIELECTRIC STRENGTH: 250 V AC min.  
 CONTACT RESISTANCE: 100 mΩ max. initial.  
 INSULATION RESISTANCE: 10<sup>11</sup> Ω min.

**Environmental**

OPERATING TEMPERATURE: -40°C to 85°C

A4				 <b>ROC PU</b>	COMMON TOLERANCE:	UNIT	MM	PROJECTED		PRODUCT NAME:	
A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:	TPS645-5NC105
A2					X.XX	± 0.10	DATE	2017	APPROVAL BY	ALEN	Https: www.rocpu.tw
A1					X.X	± 0.15	<h1>ROC PU TECHNOLOGY CO., LTD</h1>				
REV.	DATE	REVISION	DESCRIPTION		ISSUE	X					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				