



Mechanical

ACTUATION FORCE: 100 grams, 160 grams, 200 grams, 260 grams
 LIFE EXPECTANCY: 100,000 operations.

Electrical

CONTACT RATING: 50 mA @ 12 V DC.
 DIELECTRIC STRENGTH: 250 V AC min.
 CONTACT RESISTANCE: 100 mΩ max. initial.
 INSULATION RESISTANCE: 10¹¹ Ω min.

Environmental

OPERATING TEMPERATURE: -40°C to 85°C

A4				
A3				
A2				
A1				
REV.	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE:	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TPS645-5NC60
DATE	2017	APPROVAL BY	ALEN	Https: www.rocpu.tw
ROC PU TECHNOLOGY CO., LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				