

BU-P2854-@

(Panel Mount 4mm Banana Jack, 10 Pack)



- BU-P2854 is a 10-pack of panel mountable 4mm banana jacks. Can be mounted to panels from 0.063" to 0.375" thick. Wire can be soldered to pin ends.
- Overall length 1.22" (31mm), OD = 0.5" (12.7mm)
- Mounting: Mount thru panels up to 0.375" (9.52mm) thick with a \varnothing 0.375" (9.52mm) hole.
- Material: Contacts Gold-plated brass
 Insulators Nylon
- Rating: Current 15 Amps
 Voltage Handheld 30 Vrms/60 Vdc
 Hands-free testing up to 2000 VDC max
 Temperature -50°C to 120°C
- Color: The "@" in the model number indicates color.
 Available colors are: -0 Black, -2 Red
- **10 banana jacks packaged per bag.**
- RoHS 3 compliant, exemption 6c