


CT05E-04S310-1

Former P/N: CT05ES-04310-1

Rev. 5-2023
RoHS3 & REACH
Electromagnetic Sound Transducers




Operating Characteristics

ELECTRICAL

Rated Voltage	3.0 Vo-p
Operating Voltage	2.5 to 4.5 Vo-p
Coil Resistance	10 ± 1.5 Ω
Max Current at V Rated	120 mA

ACOUSTIC

Min SPL at V Rated	80 dB
Test Conditions	10 cm
f _o	3100 Hz



Physical Characteristics


MATERIAL

Housing	LCP
Diaphragm	Iron
Solder Pad	DSn (Brass)

TEMPERATURE RANGES

Operating	-40 to +85 °C
Storage	-40 to +85 °C

Weight	0.3 g
--------	-------



General tolerance = ±0.5 mm and all measurements in mm unless otherwise noted.

Revision	Description	By	Date
4-2020	Updated Mechanical Drawing - added default tol. +/- 0.5 mm, default resonant freq. tol. +/- 500 Hz	WS	2020-09-08
5-2023	Updated photo. Updated to 2-page format.	CT	2023-01-24

Warranty: For a period of one (1) year from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied, with respect to accuracy, completeness or results is extended and no liability is assumed. Challenge Electronics reserves the right to make changes in any specification, data or material contained herein.