
RoHS COMPLIANT



Electrical Characteristics

Nominal Impedance: Non-constant Frequency Range: DC to 300 MHz

Operating Voltage (rms): 500 V maximum at sea level 1500 M maximum at sea level 1500 M

Mechanical Characteristics

Mating Cycles: 500 cycles minimum
Interface Dimensions: Conform to MIL-C-39012

Environmental Characteristics

Temperature Range: -55 °C to +85 °C

	PART	DESCRIPTION
1	Body	Brass, nickel plated
2	Dielectric	POM
3	Contact	Brass, gold plated

CAD Issue	SN	2	02 Oct 02	
First Issue	SN	1	10 May 01	
DESCRIPTION OF REVISION	APPVD	ISS	DATE	



Cinch Connectivity Solutions 7-13 Russel Way, Widford Industrial Estate, Chelmsford,Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515

Fax: +44 (0) 1245 358938

SCALE: Not To Scale

DRAWN BY:

S Nash

DIMENSIONS: mm

CHECKED BY:

P Couzens

TOLERANCES:

± 0.2mm unless
otherwise stated

DATE:

02 Oct 02

TITLE:

BNC Plug to UHF Jack

PART NUMBER:

VA205

PAGE: 1 of 1