


1

2

3

4

5




Specifications:

Current Rating: 1.0A AC,DC
 Contact Resistance: 50m ohm.Max
 Insulation Resistance: 100M ohm.Min
 Withstanding Voltage: 100V AC/Minute

Material:

Insulator: Nylon6T(UL94V-0), Black
 Back Cover: LCP(UL94V-0), Black
 Contact: Phosphor Bronze
 Finish: 15u" Gold/Tin Plated
 Front Shell: SUS304, Nickel Plated
 Hook: SUS301
 Upper SPCC: SPCC, Nickel Plated
 Lower SPCC: SPCC, Nickel Plated



RoHS Compliant

DRAWN:

GENERAL TOLERANCE:

.X=±0.20
.XX=±0.15

CnC Tech

Industrial Cable and Connector Technology

CHECKED:

UNIT: MM

DESCRIPTION:

Micro USB 3.0,10P,B/M,
Solder Assembly Type,15u"

SIZE

APPROVAL:


SCALE:1:1

PART NO:

1003-026-22300

A4

PROJECTION:



REV

DATE

FILE

BY

05-FEB-2020

A

B

C

D