

HLMP-Yxxx

3-mm LED Lamps

Description

Broadcom tests parts at the absolute maximum rated conditions recommended for the device. The actual performance that you obtain from Broadcom[®] parts depends on the electrical and environmental characteristics of your application, but will probably be better than the performance outlined in the table.

Table 1: Reliability Tests

Test Name	Reference	Test Conditions	Units Tested	Units Failed
High Temperature Operating Life	JESD22-A108	$T_A = 100^{\circ}\text{C}$, $I_F = 7\text{ mA}$ for 1000 hours	56	0
Low Temperature Operating Life	JESD22-A108	$T_A = -40^{\circ}\text{C}$, $I_F = 20\text{ mA}$ for 1000 hours	56	0
Temperature Humidity Operating Life	JEITA ED-4701/100 102	$T_A = 85^{\circ}\text{C}$, 85% RH, $I_F = 17\text{ mA}$ for 500 hours	56	0
Temperature Cycle	JESD22-A104	$-40^{\circ}\text{C}/100^{\circ}\text{C}$, 15-minute dwell, 5-minute transfer, 100 cycles	336	0
High Temperature Storage Life	JESD22-A103	$T_A = 100^{\circ}\text{C}$ for 1000 hours	56	0
Low Temperature Storage	JESD22-A119	$T_A = -40^{\circ}\text{C}$ for 1000 hours	56	0
Temperature Humidity Storage Life	JEITA ED-4701/100 103	$T_A = 85^{\circ}\text{C}$, 85% RH for 1000 hours	56	0
Solderability	J-STD-002	245°C for 5 seconds	28	0
Solder Heat Resistance	JESD22-B106	260°C \pm 5°C for 10 seconds \pm 5 seconds	28	0

NOTE: A failure is any LED that is open or shorted or that failed to emit light (except for the Solderability test).

Disclaimer

Broadcom's products are not specifically designed, manufactured, or authorized for sale as parts, components, or assemblies for the planning, construction, maintenance, or direct operation of a nuclear facility or for use in medical devices or applications. The customer is solely responsible, and waives all rights to make claims against Broadcom or its suppliers, for all loss, damage, expense, or liability in connection with such use.

Broadcom, the pulse logo, Connecting everything, Avago Technologies, Avago, and the A logo are among the trademarks of Broadcom and/or its affiliates in the United States, certain other countries, and/or the EU.

Copyright © 2021 Broadcom. All Rights Reserved.

The term "Broadcom" refers to Broadcom Inc. and/or its subsidiaries. For more information, please visit www.broadcom.com.

Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.