8501RSD34V53

Plug in relay, Type R, hermetically sealed miniature, 5A resistive at 240 VAC, 14 blade, 4PDT, 4 NO, 4 NC, 24 VDC coil





Main		
Product range	8501R	
Product type	Miniature Relay	
Relay Type	Low voltage	

Complementary

Mounting type	Socket	
Contact composition	4PDT	
[Uc] control circuit voltage	24 V DC	
Pilot light	No indicator	
Manual operator	Without test button	
Horsepower rating	Not rated	
Breaking capacity	5 A 120 V AC resistive control circuit UL 508 5 A 240 V AC resistive control circuit UL 508 5 A 30 V DC resistive control circuit UL 508	
Maximum switching voltage	30 V DC 240 V AC	
Contact material	Hermetically sealed silver tin oxide	
Operating time	20 ms - pick-up 20 ms - drop-out	
Shape of pins	Spade	
For use with	8501NR45	
Height	1.16 in (29.4 mm)	
Width	0.91 in (23.1 mm)	
Depth	1.53 in (38.9 mm)	

Environment

Ambient temperature range - operational	-40131 °F (-4055 °C)
Product certifications	UL Listed UL Recognized CSA CE

Ordering and shipping details

Category	21143 - 8501 R	
Discount Schedule	CP2	
GTIN	785901031895	
Nbr. of units in pkg.	1	
Package weight(Lbs)	1.76 oz (49.895 g)	

Returnability	Yes
Country of origin	CN
Packing Units	
Unit Type of Package 1	PCE
Package 1 Height	1.30 in (3.302 cm)
Package 1 width	1.50 in (3.81 cm)
Package 1 Length	2.10 in (5.334 cm)
Offer Sustainability	
Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEU RoHS
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	₫Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

18 months

Contractual warranty

Warranty